

# NVG-7



*u s e r ' s   g u i d e*

**AMERICAN  
TECHNOLOGIES  
NETWORK  
CORP.**





The information in this manual furnished for information use only, is subject to change without notice, is not to be construed as a commitment by ATN Corp.

ATN Corp. assumes no responsibility or liability for any errors or inaccuracies that may appear in this book.

©2002 ATN Corp. All right reserved.

# FEATURES

---

- High Quality US 2<sup>nd</sup> or 3<sup>rd</sup> gen. light intensifier tube
- Super fast lens system provides the user with a clear and sharp image
- Dual eye viewing system for long viewing sessions
- Built-in Infra Red illuminator lets you see even in total darkness
- Interchangeable lenses for different magnification
- Head or helmet mounted for hands free use
- Rugged and versatile design
- Easy to use digital controls
- Two years warranty (optional extended warranty)

# SPECIFICATIONS

---

Magnification .....	1X (4X with doubler)
Intensifier tube .....	US Gen. 2+ or Gen.3
Detection range .....	100(Gen.2) or 180(Gen.3) m/y
Recognition range .....	150(Gen.2) or 200(Gen.3) m/y
Lens System .....	35 mm; F1:1.2
Field of view .....	40°
Range of Focus.....	0.25m to ∞
Power Supply.....	1.5 volt AA size
Battery Life .....	10 hours
Operating Temp .....	-30°F to +110°F
Dimensions.....	172x62x102 mm (6.7" x 2.5" x 4")
Weight.....	0.45kg (0.9 lb)

# APPLICATION

---

Compact and lightweight, the NVG-7 night vision goggles are similar to the widely available PVS-7 goggles (standard PVS-7 is 50% heavier and 100% larger). Rugged (metal not plastic), and a top-notch performer the NVG7 is an exceptional choice for hands free usage.

The NVG-7 goggles have a built in IR for total darkness with indicator "ON" light within the FOV and a flip-up headset.

The NVG7 is available with a wide range of image intensifier options to meet a wide array of specification requirements.

The NVG-7 night vision goggles is a complex optoelectronic system for individual use. The device consists of the objective lens assembly, eyepiece and the body. The body contains a image intensifier tube assembly with an integrated high voltage power source and the battery housing.

Objective lens protective cover (not shown) is intended to protect the objective lens from dust and scratches. It also will act as a daylight filter, allowing you to test the scope in daylight or other bright light situations. The pinhole in the center of the protective cover allows the user to check the operation ability of the device in daylight conditions.

**NOTE:** Do not test the scope in daylight conditions even with the daylight filter/lens cap on for more than ten (10) minutes.


# OPERATION

---

- Take the monocular out of the case.
- Install the battery into the housing with the polarity order as shown on the scope. Battery Type: 1.5 Volt, AA size .
- Press the button (short press - less than 1.5 sec.) to turn the unit on by the protective lens cover still attached to the lens. **Do not turn the unit on in the daytime without the protective lens cap on.** You should see green glow in the eyepiece.
- Observe the scene and adjust the diopter for optimal image clarity.
- You may now enter a dark environment or simply shut the lights off in order to darken the room.
- Next, remove the lens cap/daylight filter. Adjust the front lens for the distance of the focus. You should not have to readjust the diopter.
- To turn the unit off, push the button again by short press (less than 1.5 sec.).

# FOCUSING

---



To focus the NVG-7, first you will need to adjust the diopter. Simply turn the diopter clockwise until it stops. Then, while looking through the diopter at an object, slowly turn the diopter back counter clockwise until the grain in the image is sharp.

**NOTE:** We suggest that you focus the diopter during daylight with the filter on.

Next focus the front lens until the image and the grain are both sharp. When you are in low-light conditions and the daylight filter is off, you may focus the front lens to receive sharp image, the diopter should not be adjusted.

**NOTE:** The front lens should be readjusted as you view objects at different distances.

# INFRA-RED ILLUMINATOR

---



Infra-red illuminators, or IR illuminators, are common to night vision. The IR light greatly enhances the performance of the NVG-7 while remaining almost totally invisible to the naked eye.

The NVG-7 goggles have a built in IR with indicator "ON" light within the FOV. To turn the IR on, push the button by long press (more than 1.5 sec.). It is important to remember that the IR illuminator is simply an infra red light source, and like any light source, it may lose its effectiveness over a great distance.

To turn the IR off, push the button again by long press (more than 1.5 sec.).

**NOTE:** The IR will automatically turn off when the unit's power is turned off.

# FLIP-UP HEADSET

---

## PART I

- 1) The first step that you want to take in mounting NVG-7 on your head is to fit the headgear to your size. Adjust the headgear first before attaching the NVG-7 to it.
- 2) Loosen all the straps and place the headgear on your head.
- 3) You will want to tighten the straps.

## PART II

Now you are ready to mount the NVG-7 on to your headgear.

- 1) Remove the already adjusted headgear from your head.
- 2) Slide the NVG-7 on to the rail.



# F100 FRONT LENS *(optional)*

---



F100 Front Lens

The NVG-7 with F100 front lens can be used as a powerful night vision bi-ocular. To change the front lens unscrew the front lens off the body of the NVG-7 (make sure that the unit is turned off). Screw the F100 lens.

# STORAGE AND CARE

---

- If the device is not to be used for extended period of time (more than 10 days) remove the battery.
- Avoid touching lenses. If fingerprints or traces of dirt or dust appear, clean their surface with a Photographic lens cleaning tissue.
- Keep lens cap/daylight filter on when not in use.
- The NVG-7 is not harmful to the user or the environment.
- Do not disassemble except to clean the front lens and eyepiece: **it will void your warranty.**
- Evaluate the scope function by looking through it in a lit environment **with the daylight filter lens cap on. Never use in daylight without the daylight filter lens cap on.**
- **Never point the NVG-7 at a bright light source.**
- Adverse atmospheric conditions such as fog, smog, or haze and a lack of ambient light (moon or starlight) may diminish the effective viewing distance.

# TROUBLE SHOOTING

---

**Q:** Flashes, flickers, or clicking occur while operating

**S:** If it occurs within the first five minutes of inserting new batteries, it is normal and the device will resume normal operation soon thereafter. If it occurs for more than 10 minutes, contact for service instructions.

**Q:** Dark spots on screen.

**S:** These are either cosmetic blemishes in the intensifier tube or dust particles.

**Q:** Screen becomes darker than at previous use.

**S:** Replace batteries. If problem persists, contact your dealer or other authorized service representative for service instructions.

**Q:** Image not clear.

**S:** Adjust objective lens, and/or the eyepiece.

## 2 YEAR PRODUCT WARRANTY

---

This product is guaranteed to be free from manufacturing defects in material and workmanship under normal use for a period of 2 (two) years from the date of purchase. In the event a defect that is covered by the foregoing warranty occurs during the applicable period stated above, ATN, at its option, will either repair or replace the product, and such action on the part of ATN shall be the full extent of ATN's liability, and the Customer's sole and exclusive remedy. This warranty does not cover a product (a) used in other than its normal and customary manner; (b) subjected to misuse; (c) subjected to alterations, modifications or repairs by the Customer or by any party other than ATN without prior written consent of ATN; (d) special order or "close-out" merchandise or merchandise sold "as-is" by either ATN or the ATN dealer; or (e) merchandise that has been discontinued by the manufacturer and either parts or replacement units are not available due to reasons beyond the control of ATN. ATN shall not be responsible for any defects or damage that in ATN's opinion is a result from the mishandling, abuse, misuse, improper storage or improper operation, including use in conjunction with equipment which is electrically or mechanically incompatible with or of inferior quality to the product, as well as failure to maintain the environmental conditions specified by the manufacturer. **CUSTOMER IS HEREBY NOTIFIED THAT OPERATION OF THE EQUIPMENT DURING DAYLIGHT HOURS OR UNDER ANY EXCESSIVE LIGHT CONDITIONS MAY PERMANENTLY DAMAGE THE INTERNAL COMPONENTS OF THE UNIT AND SAID DAMAGE WILL NOT BE COVERED UNDER THIS WARRANTY.** This warranty is extended only to the original purchaser. Any breach of this warranty shall be waived unless the customer notifies ATN at the address noted below within the applicable warranty period.

The customer understands and agrees that except for the foregoing warranty, no other warranties written or oral, statutory, expressed or implied, including any implied warranty of merchantability or fitness for a particular purpose, shall apply to the product. All such implied warranties are hereby and expressly disclaimed.

## LIMITATION OF LIABILITY

---

ATN will not be liable for any claims, actions, suits, proceedings, costs, expenses, damages or liabilities arising out of the use of this product. Operation and use of the product are the sole responsibility of the Customer. ATN's sole undertaking is limited to providing the products and services outlined herein in accordance with the terms and conditions of this Agreement. The provision of products sold and services performed by ATN to the Customer shall not be interpreted, construed, or regarded, either expressly or implied, as being for the benefit of or creating any obligation toward any third party of legal entity outside ATN and the Customer; ATN's obligations under this Agreement extend solely to the Customer. **ATN's liability hereunder for damages, regardless of the form or action, shall not exceed the fees or other charges paid to ATN by the customer or customer's dealer. ATN shall not, in any event, be liable for special, indirect, incidental, or consequential damages, including, but not limited to, lost income, lost revenue, or lost profit, whether such damages were foreseeable or not at the time of purchase, and whether or not such damages arise out of a breach of warranty, a breach of agreement, negligence, strict liability or any other theory of liability.**

## PRODUCT WARRANTY REGISTRATION

---

In order to validate the warranty on your product, ATN must receive a completed Product Warranty Registration Card for each unit. Please complete the form below and immediately mail it to our Service Center: ATN Corporation, 20 South Linden Ave., Suite 1B, South San Francisco CA 94080. Products qualifying for warranty repair will be either repaired or replaced within 10 business days of receipt of merchandise unless the customer is notified otherwise.

## OBTAINING WARRANTY SERVICE

---

To obtain warranty service on your unit, take or send the product, postage paid, with a copy of your sales receipt to our service center, ATN Corporation at the address noted above. All merchandise must be fully insured with the correct postage; ATN will not be responsible for improper postage, or, missing or damaged merchandise during shipment. *Lortie el del ing exercil ex eumy nosto eliquat iureetuer ipit ea feum zzrisci tion er sim zzrilissit vel ing esto eniamet lupatet la augait nulputat, vul-laoz sequi et la feugie facing erit wis am zzril iustus nim esequismolore doluptat. Ut la feu feu faccum eum quipis estrud elent utpatue dunt velit lorperci euismodig ismolortie velese diam, consed*



For customer service and technical support, please contact  
American Technologies Network Corp.

**North American Office**

20 S. Linden Ave. Suite 1B, South San Francisco, CA 94080  
phone: 800-910-2862, 650-875-0130; fax: 650-875-0129

**European Office**

phone: 44(0)870-0111286, fax: 44(0) 845-3349142

The following countries can use our  
**toll free number 00 800 9102-8620**

Austria, France, Germany, Holland, Italy, Spain, Sweden, Switzerland

**[www.atncorp.com](http://www.atncorp.com)**